

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool kit, consisting of: crimping pliers for ferrules, stripping pliers, sheath stripping tool, cable cutter, bladed screwdriver: 0,6x3,5, tool organizer

Similar figure

Product description

Tool set, equipped

Your advantages

- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range
- Rugged and heavy-duty tool bags

Commercial data

Item number	1212422
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4046356503297
Weight per piece (including packing)	1,670 g
Weight per piece (excluding packing)	1,479.86 g
Customs tariff number	82060000
Country of origin	DE

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

Set consists of

CRIMPFOX DUO 16S - Crimping pliers

1202877

<https://www.phoenixcontact.com/us/products/1202877>



Crimping pliers, contact type: insulated and uninsulated ferrules, standards/regulations: DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F, cross-section, minimum: 0.14 mm², cross-section, maximum: 16 mm², for TWIN ferrules up to 2 mm² x 6 mm², automatic cross-section adjustment, rotating dies, lateral and front entry, crimping: square

WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

WIREFOX-D 40 - Stripping tool

1212161

<https://www.phoenixcontact.com/us/products/1212161>



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

CUTFOX 18 - Cable-cutting tool

1212129

<https://www.phoenixcontact.com/us/products/1212129>



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm²)

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

SZF 1-0,6X3,5 - Screwdriver

1204517

<https://www.phoenixcontact.com/us/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

<https://www.phoenixcontact.com/us/products/1212423>



Tool box, unequipped

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Square crimp

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149
-----------	----------

UNSPSC

UNSPSC 21.0	27113200
-------------	----------

TOOL-KIT STANDARD - Tool set



1212422

<https://www.phoenixcontact.com/us/products/1212422>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com