

CRIMPFOX-SR 6-1 - Crimping pliers



1212467

<https://www.phoenixcontact.com/us/products/1212467>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for MC3 solar connectors, pressure lock can be unlocked, lateral entry, with 2.5 .. 6 mm² locator

Your advantages

- Ergonomically designed handles
- Unlockable pressure lock
- Optimized mechanical transmission reduces the force required by up to 25 %
- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1212467
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3139
GTIN	4046356526937
Weight per piece (including packing)	679.4 g
Weight per piece (excluding packing)	679.4 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-SR 6-1 - Crimping pliers



1212467

<https://www.phoenixcontact.com/us/products/1212467>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---------------------------------------------------------------------------------------------------------------

Product properties

Product type	Crimping tool
Compression	Square crimp
Product property	Unlockable pressure lock
	Up to 25% lower actuation force
	Marked die stations

Connection data

Conductor connection

Cross section range, metric	2.5 mm ² ... 6 mm ²
Cross section range AWG	14 ... 10

Dimensions

Length	256 mm
--------	--------

Material specifications

Color	black
-------	-------

CRIMPFOX-SR 6-1 - Crimping pliers



1212467

<https://www.phoenixcontact.com/us/products/1212467>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212467>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-SR 6-1 - Crimping pliers



1212467

<https://www.phoenixcontact.com/us/products/1212467>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-SR 6-1 - Crimping pliers



1212467

<https://www.phoenixcontact.com/us/products/1212467>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
-----------------------------------------	-------------------------------------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com