TOOL-CASE BASIC - Toolbox

1212428

https://www.phoenixcontact.com/us/products/1212428

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool case, equipped with: cable cutter, diagonal cutter, combination and needle-nose pliers, stripping pliers, stripping tools, crimping pliers, screwdrivers, control cabinet key, sample set, box of ferrules

Commercial data

Item number	1212428
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4046356514613
Weight per piece (including packing)	6,768 g
Weight per piece (excluding packing)	6,768 g
Customs tariff number	82060000
Country of origin	DE

Set consists of

SAMPLE-TOOL-CASE - Toolbox

1208319

https://www.phoenixcontact.com/us/products/1208319



Toolbox, without instruments, with rubber straps as tool fixtures

---

CRIMPFOX 10S - Crimping pliers

1212045

https://www.phoenixcontact.com/us/products/1212045



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm^2 ... 10 mm^2, unlockable pressure lock, lateral entry

---

CRIMPFOX-RCI 6 - Crimping pliers

1212057

https://www.phoenixcontact.com/us/products/1212057



Crimping pliers, for insulated cable lugs, 0.5 mm^2 ... 6.0 mm^2 (red, blue, yellow), oval crimp, symmetrical

CUTFOX 18 - Cable-cutting tool

1212129

https://www.phoenixcontact.com/us/products/1212129



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm^2)

CUTFOX-S VDE - Diagonal cutter

1212207

https://www.phoenixcontact.com/us/products/1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

UNIFOX-C VDE - Combination pliers

1212202

https://www.phoenixcontact.com/us/products/1212202



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

UNIFOX-P VDE - Needle-nose pliers

1212204

https://www.phoenixcontact.com/us/products/1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

WIREFOX 10 - Stripping tool

1212150

https://www.phoenixcontact.com/us/products/1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm^2, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm^2 stranded/1.5 mm^2 solid, replaceable stripping blade

WIREFOX-D 11 - Stripping tool

1212160

https://www.phoenixcontact.com/us/products/1212160



Stripping tool, for stripping multicore signal, control and fiberglass wires of Ø 2.5 - 11 mm. Insulation thickness up to 1 mm

WIREFOX-D 40 - Stripping tool

1212161

https://www.phoenixcontact.com/us/products/1212161



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

SZF 0-0,4X2,5 - Screwdriver

1204504

https://www.phoenixcontact.com/us/products/1204504



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

SZF 1-0,6X3,5 - Screwdriver

1204517

https://www.phoenixcontact.com/us/products/1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

SZF 2-0,8X4,0 - Screwdriver

1204520

https://www.phoenixcontact.com/us/products/1204520



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip

SZF 3-1,0X5,5 - Screwdriver

1206612

https://www.phoenixcontact.com/us/products/1206612



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

SZS 0,4X2,5 VDE - Screwdriver

1205037

https://www.phoenixcontact.com/us/products/1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

SZS 0,5X3,0 VDE - Screwdriver

1207404

https://www.phoenixcontact.com/us/products/1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

SZS 1,0X4,0 VDE - Screwdriver

1205066

https://www.phoenixcontact.com/us/products/1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

SZS 1,0X6,5 VDE - Screwdriver

1205079

https://www.phoenixcontact.com/us/products/1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

SZK PH1 VDE - Screwdriver

1205150

https://www.phoenixcontact.com/us/products/1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

SZK PH2 VDE - Screwdriver

1205163

https://www.phoenixcontact.com/us/products/1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

SZK PZ1 VDE - Screwdriver

1206450

https://www.phoenixcontact.com/us/products/1206450



Screwdriver, PZ crosshead, VDE insulated, size: PZ 1 x 80 mm, 2-component grip, with non-slip grip

SZK PZ2 VDE - Screwdriver

1206463

https://www.phoenixcontact.com/us/products/1206463



Screwdriver, PZ crosshead, VDE insulated, size: PZ 2 x 100 mm, 2-component grip, with non-slip grip

USS 4 - Control cabinet key

1203149

https://www.phoenixcontact.com/us/products/1203149



Control cabinet key, metal, for all common types of control cabinet

SAMPLE-TOOL-CASE-CABLE-SET - Sample set

1208335

https://www.phoenixcontact.com/us/products/1208335



Tool sample set

TOOL-CASE BASIC - Toolbox

1212428

https://www.phoenixcontact.com/us/products/1212428

AI SORTI BOX RD - Assortment box

3202960

https://www.phoenixcontact.com/us/products/3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Case

Dimensions

Width	475 mm
Height	110 mm
Length	425 mm

Material specifications

Color	multicolored (RAL -)

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149

UNSPSC

UNSPSC 21.0	27113200

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com