

MICROFOX-F ESD - Flat-nosed pliers



1212484

<https://www.phoenixcontact.com/us/products/1212484>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ESD electronic flat-nose pliers, smooth grip, with opening spring, non-reflective coating and phosphate-treated, 2-component grip

Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept a different ESD-compliant material. In future, the tools will be supplied with plastic handles in black/turquoise. This does not affect the function or quality of the ESD pliers.

Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Special conductive plastic handles for slow and controlled dissipation of electrostatic energy
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- Screwed precision joint for permanent stability and optimum results
- Special tool steel for permanent use

Commercial data

Item number	1212484
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3152
GTIN	4046356527163
Weight per piece (including packing)	85.5 g
Weight per piece (excluding packing)	81 g
Customs tariff number	82032000
Country of origin	DE

MICROFOX-F ESD - Flat-nosed pliers



1212484

<https://www.phoenixcontact.com/us/products/1212484>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Electronics pliers
Product property	Uniform and smooth opening
	Ergonomically designed handle
	Two-component handle
	Screwed precision joint
	Mirror-polished and phosphated metal surfaces
	ESD tested

Electrical properties

Fuse	DIN EN 61340-5-1/VDE 0300-5-1, DIN EN 61340-2-3/VDE 0300-2-3
------	--

Dimensions

Length	125 mm
--------	--------

Material specifications

Color	multicolored (RAL -)
Material	Steel
Coating	phosphatized

MICROFOX-F ESD - Flat-nosed pliers



1212484

<https://www.phoenixcontact.com/us/products/1212484>

Classifications

ECLASS

ECLASS-13.0	21043817
ECLASS-15.0	21043817

ETIM

ETIM 10.0	EC000833
-----------	----------

UNSPSC

UNSPSC 21.0	27112100
-------------	----------

MICROFOX-F ESD - Flat-nosed pliers



1212484

<https://www.phoenixcontact.com/us/products/1212484>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com