# SF-BIT-PHSL 1-70 - Screw insert

1212479

https://www.phoenixcontact.com/us/products/1212479

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw bit, positive/negative PH/bladed, E6.3-1/4" drive, size: PH 1 x 70 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

## Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

## Commercial data

| | |
|---|---|
| Item number | 1212479 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3149 |
| GTIN | 4046356527118 |
| Weight per piece (including packing) | 11.92 g |
| Weight per piece (excluding packing) | 11.92 g |
| Customs tariff number | 82079030 |
| Country of origin | CZ |

## Technical data

### Notes

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |


### Product properties

| | |
|---|---|
| Product type | Screwdriver tools |
| Type | Phillips |
| Product property | Phillips Recess/slotted screw head |

### Connection data

| | |
|---|---|
| Output | Pozidrive/plus/minus |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Blade height | 70 mm |
| Length | 70 mm |

### Material specifications


| | |
|---|---|
| Color | silver-colored |
| Material | Steel |

### Standards and regulations

| | |
|---|---|
| Tests | DIN 3126 |

## Drawings

Dimensional drawing



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212479

**EAC**
Approval ID: RU C-DE.AI30.B.01750

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21044203 |
| ECLASS-15.0 | 21044203 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC003864 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27112800 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.452 kg CO2e |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com