

MICROFOX-S ESD - Diagonal cutter



1212480

<https://www.phoenixcontact.com/us/products/1212480>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ESD electronic diagonal cutter, round head, without chamfer, with opening spring, non-reflective coating and phosphate-treated, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1 mm diameter

Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept a different ESD-compliant material. In future, the tools will be supplied with plastic handles in black/turquoise. This does not affect the function or quality of the ESD pliers.

Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Special conductive plastic handles for slow and controlled dissipation of electrostatic energy
- Special tool steel for permanent use
- Screwed precision joint for permanent stability and optimum results
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working

Commercial data

Item number	1212480
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3152
GTIN	4046356527125
Weight per piece (including packing)	92 g
Weight per piece (excluding packing)	75.5 g
Customs tariff number	82032000
Country of origin	DE

MICROFOX-S ESD - Diagonal cutter



1212480

<https://www.phoenixcontact.com/us/products/1212480>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Electronics pliers

Product property

Screwed precision joint

Mirror-polished and oiled metal surface

Ergonomic two-component handle

Sensitive opening spring

ESD tested

Electrical properties

Fuse

DIN EN 61340-5-1/VDE 0300-5-1, DIN EN 61340-2-3/VDE 0300-2-3

Dimensions

Length

110 mm

Material specifications

Color

multicolored (RAL -)

Material

Steel

Coating

phosphatized

MICROFOX-S ESD - Diagonal cutter



1212480

<https://www.phoenixcontact.com/us/products/1212480>

Classifications

ECLASS

ECLASS-13.0	21043711
ECLASS-15.0	21043711

ETIM

ETIM 10.0	EC000165
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

MICROFOX-S ESD - Diagonal cutter



1212480

<https://www.phoenixcontact.com/us/products/1212480>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	3.239 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com