

MICROFOX-SB - Diagonal cutter



1212489

<https://www.phoenixcontact.com/us/products/1212489>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Through-connected joint for permanent stability and optimum distribution of force
- Mirror-polished and oiled metal surfaces, which provide maximum rust protection
- Special tool steel for permanent use
- For a variety of applications

Commercial data

Item number	1212489
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3151
GTIN	4046356527200
Weight per piece (including packing)	88.7 g
Weight per piece (excluding packing)	84.6 g
Customs tariff number	82032000
Country of origin	DE

MICROFOX-SB - Diagonal cutter



1212489

<https://www.phoenixcontact.com/us/products/1212489>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Electronics pliers
Product property	Push-through joint
	Mirror-polished and oiled metal surface
	Ergonomic two-component handle
	Sensitive opening spring

Dimensions

Length	115 mm
--------	--------

MICROFOX-SB - Diagonal cutter



1212489

<https://www.phoenixcontact.com/us/products/1212489>

Classifications

ECLASS

ECLASS-13.0	21043711
ECLASS-15.0	21043711

ETIM

ETIM 10.0	EC000165
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

MICROFOX-SB - Diagonal cutter



1212489

<https://www.phoenixcontact.com/us/products/1212489>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	3.254 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com