TOOL-CARRIER - Tool set

1212503

https://www.phoenixcontact.com/us/products/1212503

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool bag, equipped with: cable cutter, diagonal cutter, stripping pliers, NYM stripping tool, stripping tool for removing sheath, crimping pliers, crimping die for ferrules, combination, needle-nose, and water pump pliers, VDE screwdriver, bladed: 0.4 x 2.5/0.5 x 3.0/1.0 x 4.0/1.0 x 6.5, Philips: PHO/PH1/PH2, voltage tester, control cabinet key, knife, tape measure

Your advantages

- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range
- Rugged and heavy-duty tool bags

Commercial data

Item number	1212503
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4046356528399
Weight per piece (including packing)	4,970 g
Weight per piece (excluding packing)	4,800 g
Customs tariff number	82060000
Country of origin	DE

Set consists of

CUTFOX-S VDE - Diagonal cutter

1212207

https://www.phoenixcontact.com/us/products/1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

CUTFOX 18 - Cable-cutting tool

1212129

https://www.phoenixcontact.com/us/products/1212129



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm^2)

WIREFOX 10 VDE - Stripping tool

1212366

https://www.phoenixcontact.com/us/products/1212366



Stripping pliers, for removing the sheath from cables up to 5 mm in diameter, for stripping conductors with a cross section of up to 10 mm^2, scale for measuring the stripping length; VDE-tested.

WIREFOX-D 13 - Stripping tool

1212162

https://www.phoenixcontact.com/us/products/1212162



Stripping tool, for stripping installation lines of Ø 8 - 13 mm , e.g. NYM 3 x 1.5 mm^2 to 5 x 2.5 mm^2, single line stripping 0.2 mm^2 - 4 mm^2 , with longitudinal cut blade and sliding knife

WIREFOX-D 28 - Stripping tool

1212174

https://www.phoenixcontact.com/us/products/1212174



Stripping tool, for stripping lines of Ø 8 - 28 mm

CRIMPFOX-M - Crimping pliers

1212072

https://www.phoenixcontact.com/us/products/1212072



Basic pliers, for accommodating dies for a wide range of type of contacts

CRIMPFOX-M 10/DIE - Crimp insert

1212080

https://www.phoenixcontact.com/us/products/1212080



Die, for Crimpfox-M, for ferrules 0.25 - 10 mm^2, packed in a serial storage box

UNIFOX-CE VDE - Combination pliers

1212203

https://www.phoenixcontact.com/us/products/1212203



Combination pliers, angled design, with opening spring and locking device, cross-notched grip area, integrated M8 - M10 ring wrench, VDE 1000 V AC/1500 V DC tested

UNIFOX-P VDE - Needle-nose pliers

1212204

https://www.phoenixcontact.com/us/products/1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

UNIFOX-WP - Water pump pliers

1212365

https://www.phoenixcontact.com/us/products/1212365



Water pump pliers, with groove joint, grip areas with dual notching, acc. to VDE ISO 8976

SZS 0,4X2,5 VDE - Screwdriver

1205037

https://www.phoenixcontact.com/us/products/1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

SZS 0,5X3,0 VDE - Screwdriver

1207404

https://www.phoenixcontact.com/us/products/1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

SZS 1,0X4,0 VDE - Screwdriver

1205066

https://www.phoenixcontact.com/us/products/1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

SZS 1,0X6,5 VDE - Screwdriver

1205079

https://www.phoenixcontact.com/us/products/1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

SZK PH0 VDE - Screwdriver

1205147

https://www.phoenixcontact.com/us/products/1205147



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

SZK PH1 VDE - Screwdriver

1205150

https://www.phoenixcontact.com/us/products/1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

SZK PH2 VDE - Screwdriver

1205163

https://www.phoenixcontact.com/us/products/1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

DUSPOL EXPERT - Voltage tester

1209091

https://www.phoenixcontact.com/us/products/1209091



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

USS 4 - Control cabinet key

1203149

https://www.phoenixcontact.com/us/products/1203149



Control cabinet key, metal, for all common types of control cabinet

TOOL-CARRIER EMPTY - Toolbag, unequipped

1212499

https://www.phoenixcontact.com/us/products/1212499



Toolbag, unequipped, black

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Bag

Dimensions

Width	185 mm
Height	220 mm
Length	290 mm

Material specifications

Color	black (RAL 9005)

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149

UNSPSC

UNSPSC 21.0	27113200

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com