

SF-ASD 21 - Cordless screwdriver



1212532

<https://www.phoenixcontact.com/us/products/1212532>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cordless screwdriver, including battery, forward/reverse running, 21 clutch settings, up to 600 rpm, 6.3 mm hexagonal fast-connection drill chuck, torque can be adjusted from 0.3 Nm ... 4.4 Nm

Your advantages

- Cordless screwdriver with two-speed gearbox, forward/reverse running and 21-stage clutch with drilling stage of up to 600 rpm
- Adjustable from 0.3 ... 4.4 Nm
- Integrated LEDs ensures the illumination of the workspace
- With optional snap-on protective cap to prevent unintentional torque adjustment

Commercial data

Item number	1212532
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3243
GTIN	4046356589673
Weight per piece (including packing)	765.7 g
Weight per piece (excluding packing)	742.8 g
Customs tariff number	84672920
Country of origin	JP

SF-ASD 21 - Cordless screwdriver



1212532

<https://www.phoenixcontact.com/us/products/1212532>

Technical data

Product properties

Product type	Torque tool
Type of packaging	packed in cardboard
Battery-operated voltage	3.6 V
Product property	Cordless screwdriver with two-speed gear and forward/reverse running 21-stage clutch with drilling setting up to 600 rpm

Electrical properties

Power consumption	5.4 W
Nominal voltage U_N	3.6 V DC

Battery

Battery-operated voltage	3.60 V DC
Battery capacity	1.90 Ah

Connection data

Torque range	0.3 Nm ... 4.4 Nm
Output	6,3 mm

Dimensions

Width	44 mm
Height	165 mm
Length	277 mm

SF-ASD 21 - Cordless screwdriver



1212532

<https://www.phoenixcontact.com/us/products/1212532>

Classifications

ECLASS

ECLASS-13.0	21050804
ECLASS-15.0	21050804

ETIM

ETIM 10.0	EC001396
-----------	----------

UNSPSC

UNSPSC 21.0	27111700
-------------	----------

SF-ASD 21 - Cordless screwdriver



1212532

<https://www.phoenixcontact.com/us/products/1212532>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	29.801 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com