

# SF-BIT-SL 0,5X3,0-50 - Screw insert



1212566

<https://www.phoenixcontact.com/us/products/1212566>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw bit, bladed, E6.3-1/4" drive, size: 0.5 x 3.0 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

## Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

## Commercial data

Item number	1212566
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3149
GTIN	4046356590013
Weight per piece (including packing)	6.8 g
Weight per piece (excluding packing)	7 g
Customs tariff number	82079030
Country of origin	CZ

# SF-BIT-SL 0,5X3,0-50 - Screw insert



1212566

<https://www.phoenixcontact.com/us/products/1212566>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration


### Product properties

Product type	Screwdriver tools
Type	Bladed
Product property	Slotted screw head

### Connection data

Output	Bladed
--------	--------

### Dimensions

Dimensional drawing	
Blade width	3 mm
Blade height	50 mm
Length	50 mm
Blade thickness	0.5 mm

### Material specifications

Color	silver-colored
Material	Steel

### Standards and regulations

Tests	DIN 3126 drive, output 3127-1
-------	-------------------------------

# SF-BIT-SL 0,5X3,0-50 - Screw insert


1212566

<https://www.phoenixcontact.com/us/products/1212566>



## Drawings

Dimensional drawing



# SF-BIT-SL 0,5X3,0-50 - Screw insert



1212566

<https://www.phoenixcontact.com/us/products/1212566>

## Classifications

### ECLASS

ECLASS-13.0	21044204
ECLASS-15.0	21044204

### ETIM

ETIM 10.0	EC003864
-----------	----------

### UNSPSC

UNSPSC 21.0	27112800
-------------	----------

# SF-BIT-SL 0,5X3,0-50 - Screw insert



1212566

<https://www.phoenixcontact.com/us/products/1212566>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.316 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)