

SF-BIT-SL 0,6X3,5-70 - Screw insert



1212569

<https://www.phoenixcontact.com/us/products/1212569>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw bit, slot, E6.3-1/4" drive, Size: 0.6 x 3.5 x 70 mm, hardened, suitable for holders as per DIN 3126-F 6.3 / ISO 1173

Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

Commercial data

Item number	1212569
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3149
GTIN	4046356590044
Weight per piece (including packing)	9.74 g
Weight per piece (excluding packing)	9.71 g
Customs tariff number	82079030
Country of origin	CZ

SF-BIT-SL 0,6X3,5-70 - Screw insert



1212569

<https://www.phoenixcontact.com/us/products/1212569>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Screwdriver tools
Type	Bladed

Connection data

Output	Bladed
--------	--------

Dimensions

Blade width	3.5 mm
Blade height	70 mm
Length	70 mm
Blade thickness	0.6 mm

Material specifications

Color	silver
Material	Steel

Standards and regulations

Tests	DIN 3126 drive, output 3127-1
-------	-------------------------------

SF-BIT-SL 0,6X3,5-70 - Screw insert



1212569

<https://www.phoenixcontact.com/us/products/1212569>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212569>



EAC

Approval ID: RU C-DE.AI30.B.01750

SF-BIT-SL 0,6X3,5-70 - Screw insert



1212569

<https://www.phoenixcontact.com/us/products/1212569>

Classifications

ECLASS

ECLASS-13.0	21044204
ECLASS-15.0	21044204

ETIM

ETIM 10.0	EC003864
-----------	----------

UNSPSC

UNSPSC 21.0	27112800
-------------	----------

SF-BIT-SL 0,6X3,5-70 - Screw insert



1212569

<https://www.phoenixcontact.com/us/products/1212569>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.389 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com