

SF-BIT-SL 1,2X6,5-70 - Screw insert



1212577

<https://www.phoenixcontact.com/us/products/1212577>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw bit, bladed, E6.3-1/4" drive, size: 1.2 x 6.5 x 70 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212577 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3149 |
| GTIN | 4046356590129 |
| Weight per piece (including packing) | 16.64 g |
| Weight per piece (excluding packing) | 16.64 g |
| Customs tariff number | 82079030 |
| Country of origin | CZ |

SF-BIT-SL 1,2X6,5-70 - Screw insert



1212577

<https://www.phoenixcontact.com/us/products/1212577>

Technical data

Notes

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Product properties

| | |
|--------------|-------------------|
| Product type | Screwdriver tools |
| Type | Bladed |

Connection data

| | |
|--------|--------|
| Output | Bladed |
|--------|--------|

Dimensions

| | |
|-----------------|--------|
| Blade width | 6.5 mm |
| Blade height | 70 mm |
| Length | 70 mm |
| Blade thickness | 1.2 mm |

Material specifications

| | |
|----------|----------------|
| Color | silver-colored |
| Material | Steel |

Standards and regulations

| | |
|-------|-------------------------------|
| Tests | DIN 3126 drive, output 3127-1 |
|-------|-------------------------------|

SF-BIT-SL 1,2X6,5-70 - Screw insert



1212577

<https://www.phoenixcontact.com/us/products/1212577>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212577>



EAC

Approval ID: RU C-DE.AI30.B.01750

SF-BIT-SL 1,2X6,5-70 - Screw insert



1212577

<https://www.phoenixcontact.com/us/products/1212577>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21044204 |
| ECLASS-15.0 | 21044204 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003864 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27112800 |
|-------------|----------|

SF-BIT-SL 1,2X6,5-70 - Screw insert



1212577

<https://www.phoenixcontact.com/us/products/1212577>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.389 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com