

WIREFOX-E 10 - Stripping tool



1212706

<https://www.phoenixcontact.com/us/products/1212706>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Product description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

Your advantages

- Flexible, adjustable limit stop for the stripping length
- Stripping tool with ergonomically shaped pliers
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Commercial data

Item number	1212706
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3121
GTIN	4046356783613
Weight per piece (including packing)	254.4 g
Weight per piece (excluding packing)	253 g
Customs tariff number	82032000
Country of origin	SE

WIREFOX-E 10 - Stripping tool

1212706

<https://www.phoenixcontact.com/us/products/1212706>



Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Stripping tool
Application	Standard
Product property	Automatic adjustment mechanism
	Replaceable stripping blade
	Length stop for setting the stripping length
	Angled pliers contour
	Integrated wire cutter

Connection data

Conductor connection

Cross section range, metric	0.02 mm ² ... 10 mm ² (Stripping range)
	1.5 mm ² (Cutting zone)
Cross section range AWG	34 ... 8 (Stripping range)
	16 (Cutting zone)
Stripping length	2 mm ... 18 mm

Dimensions

Width	20 mm
Height	90 mm
Length	191 mm

Material specifications

Color	black/green
-------	-------------

WIREFOX-E 10 - Stripping tool



1212706

<https://www.phoenixcontact.com/us/products/1212706>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212706>



EAC

Approval ID: RU x-DE.xx08.B.02974

WIREFOX-E 10 - Stripping tool



1212706

<https://www.phoenixcontact.com/us/products/1212706>

Classifications

ECLASS

ECLASS-13.0	21043706
ECLASS-15.0	21043706

ETIM

ETIM 10.0	EC002109
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

WIREFOX-E 10 - Stripping tool



1212706

<https://www.phoenixcontact.com/us/products/1212706>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com