

CRIMPFOX-CATV 8,23-1 - Crimping pliers



1212717

<https://www.phoenixcontact.com/us/products/1212717>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for CATV connectors, 6.65 mm, 8.23 mm, 9.70 mm, three marked die stations, unlockable pressure lock, lateral entry

Your advantages

- Unlockable pressure lock
- Lateral conductor entry
- Crimping pliers for processing coaxial CATV connectors

Commercial data

Item number	1212717
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3138
GTIN	4046356857666
Weight per piece (including packing)	675.6 g
Weight per piece (excluding packing)	675.6 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-CATV 8,23-1 - Crimping pliers



1212717

<https://www.phoenixcontact.com/us/products/1212717>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

HEX crimp

Product property

Unlockable pressure lock

Lateral conductor entry

Crimping pliers for processing coaxial connectors

Crimping position 1

Crimping width

6.65 mm

Crimping position 2

Crimping width

8.23 mm

Crimping position 3

Crimping width

9.70 mm

Connection data

Conductor connection

Cross section range, metric

6.65 mm² ... 9.7 mm²

Dimensions

Width

22 mm

Height

80 mm

Length

256 mm

External dimensions

Outside diameter

6.65 mm ... 9.7 mm

Material specifications

Color

black

CRIMPFOX-CATV 8,23-1 - Crimping pliers



1212717

<https://www.phoenixcontact.com/us/products/1212717>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212717>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-CATV 8,23-1 - Crimping pliers



1212717

<https://www.phoenixcontact.com/us/products/1212717>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-CATV 8,23-1 - Crimping pliers



1212717

<https://www.phoenixcontact.com/us/products/1212717>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com