

# CRIMPFOX-M SCA 2,5/DIE - Crimp insert



1212742

<https://www.phoenixcontact.com/us/products/1212742>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die, for CRIMPFOX-M, for uninsulated, left angled slip-on sleeves 6.3 mm, 1.0 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, B crimp

## Your advantages

- Die for CRIMPFOX universal pliers

## Commercial data

Item number	1212742
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Z
GTIN	4046356858014
Weight per piece (including packing)	79.5 g
Weight per piece (excluding packing)	79.5 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-M SCA 2,5/DIE - Crimp insert



1212742

<https://www.phoenixcontact.com/us/products/1212742>

## Technical data

### Product properties

Product type	Die
Compression	B crimp
Product property	Replacement insert for CRIMPFOX-M universal crimping pliers

### Crimping position 1

Min. cross section	1 mm <sup>2</sup>
Max. cross section	2.5 mm <sup>2</sup>
AWG min	18
AWG max	14

# CRIMPFOX-M SCA 2,5/DIE - Crimp insert



1212742

<https://www.phoenixcontact.com/us/products/1212742>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212742>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-M SCA 2,5/DIE - Crimp insert



1212742

<https://www.phoenixcontact.com/us/products/1212742>

## Classifications

### ECLASS

ECLASS-13.0	21043852
ECLASS-15.0	21043852

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-M SCA 2,5/DIE - Crimp insert



1212742

<https://www.phoenixcontact.com/us/products/1212742>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)