

# CRIMPFOX-RCT 16-1 - Crimping pliers



1212731

<https://www.phoenixcontact.com/us/products/1212731>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimping pliers, for uninsulated tubular cable lugs, 4 - 16 mm<sup>2</sup>, indent and HEX crimp



## Your advantages

- Unlockable pressure lock
- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working
- Crimping pliers for uninsulated tube lugs
- Compact and lightweight design

## Commercial data

Item number	1212731
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3133
GTIN	4046356857901
Weight per piece (including packing)	701.6 g
Weight per piece (excluding packing)	701.6 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-RCT 16-1 - Crimping pliers



1212731

<https://www.phoenixcontact.com/us/products/1212731>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Indent crimp
Product property	Narrow head area for confined environments
	High gear ratio
	Two-hand operation
	Unlockable pressure lock

#### Crimping position 1

Min. cross section	4 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	11
AWG max	10

#### Crimping position 2

Max. cross section	10 mm <sup>2</sup>
AWG max	8

#### Crimping position 3

Max. cross section	16 mm <sup>2</sup>
AWG max	5

### Connection data

#### Conductor connection

Cross section range, metric	4 mm <sup>2</sup> ... 16 mm <sup>2</sup>
Cross section range AWG	11 ... 5

### Dimensions

Width	30 mm
Height	70 mm
Length	304 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX-RCT 16-1 - Crimping pliers



1212731

<https://www.phoenixcontact.com/us/products/1212731>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212731>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-RCT 16-1 - Crimping pliers



1212731

<https://www.phoenixcontact.com/us/products/1212731>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-RCT 16-1 - Crimping pliers



1212731

<https://www.phoenixcontact.com/us/products/1212731>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)