

CRIMPFOX 50R CUS - Crimping pliers



1212766

<https://www.phoenixcontact.com/us/products/1212766>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 35 mm² ... 50 mm², lateral entry, WM crimp

The figure shows CRIMPFOX-RCI
6 CUS

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25 %

Commercial data

Item number	1212766
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356942935
Weight per piece (including packing)	693.4 g
Weight per piece (excluding packing)	679.2 g
Country of origin	SE

CRIMPFOX 50R CUS - Crimping pliers



1212766

<https://www.phoenixcontact.com/us/products/1212766>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	WM crimp

Connection data

Conductor connection

Cross section range, metric	35 mm ² ... 50 mm ²
Cross section range AWG	2 ... 1

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

CRIMPFOX 50R CUS - Crimping pliers



1212766

<https://www.phoenixcontact.com/us/products/1212766>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212766>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 50R CUS - Crimping pliers



1212766

<https://www.phoenixcontact.com/us/products/1212766>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 50R CUS - Crimping pliers



1212766

<https://www.phoenixcontact.com/us/products/1212766>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com