

CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 0.25 mm² ... 6 mm², lateral entry, trapezoidal crimp

Your advantages

- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Unlockable pressure lock
- Comprehensive range of crimping pliers
- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1212770
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356942973
Weight per piece (including packing)	533.4 g
Weight per piece (excluding packing)	530.3 g
Country of origin	SE

CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	Trapezoidal crimp

Connection data

Conductor connection

Cross section range, metric	0.25 mm ² ... 6 mm ²
Cross section range AWG	24 ... 10

Dimensions

Width	22.5 mm
Height	72 mm
Length	220 mm

Material specifications

Color	black
-------	-------


CRIMPFOX 6T CUS - Crimping pliers

1212770

<https://www.phoenixcontact.com/us/products/1212770>

Drawings

Product drawing



CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212770>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

Classifications

UNSPSC

UNSPSC 21.0	27111518
-------------	----------

CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com