

# CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Crimping pliers**, laser marked according to customer specifications, for ferrules according to DIN 46228 Parts 1+4, 0.25 mm<sup>2</sup> ... 6 mm<sup>2</sup>, lateral entry, trapezoidal crimp

## Your advantages

- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Unlockable pressure lock
- Comprehensive range of crimping pliers
- Marked die stations for precise processing of corresponding cross sections

## Commercial data

Item number	1212770
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356942973
Weight per piece (including packing)	533.4 g
Weight per piece (excluding packing)	530.3 g
Country of origin	SE

# CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Crimping tool

Compression

Trapezoidal crimp

### Connection data

#### Conductor connection

Cross section range, metric

0.25 mm<sup>2</sup> ... 6 mm<sup>2</sup>

Cross section range AWG

24 ... 10

### Dimensions

Width

22.5 mm

Height

72 mm

Length

220 mm

### Material specifications

Color

black

# CRIMPFOX 6T CUS - Crimping pliers


1212770

<https://www.phoenixcontact.com/us/products/1212770>



## Drawings

Product drawing



# CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212770>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

## Classifications

### UNSPSC

UNSPSC 21.0	27111518
-------------	----------

# CRIMPFOX 6T CUS - Crimping pliers



1212770

<https://www.phoenixcontact.com/us/products/1212770>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)