

# CRIMPFOX-RC 2,5 CUS - Crimping pliers



1212777

<https://www.phoenixcontact.com/us/products/1212777>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for uninsulated cable lugs, 0.34 - 2.5 mm<sup>2</sup>, indent crimp

The figure shows CRIMPFOX 6 CUS

## Your advantages

- For processing uninsulated cable lugs
- Unlockable pressure lock
- Lateral conductor entry
- Marked die stations for precise processing of corresponding cross sections
- Compact and lightweight design
- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working
- Consistently high crimping quality

## Commercial data

Item number	1212777
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356943048
Weight per piece (including packing)	438.4 g
Weight per piece (excluding packing)	435.3 g
Country of origin	SE

# CRIMPFOX-RC 2,5 CUS - Crimping pliers



1212777

<https://www.phoenixcontact.com/us/products/1212777>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Crimping tool

Compression

Indent crimp

### Connection data

#### Conductor connection

Cross section range, metric

0.75 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>

Cross section range AWG

22 ... 14

### Dimensions

Width

18 mm

Height

59 mm

Length

198 mm

# CRIMPFOX-RC 2,5 CUS - Crimping pliers




1212777

<https://www.phoenixcontact.com/us/products/1212777>

## Drawings

Product drawing



# CRIMPFOX-RC 2,5 CUS - Crimping pliers



1212777

<https://www.phoenixcontact.com/us/products/1212777>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212777>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-RC 2,5 CUS - Crimping pliers



1212777

<https://www.phoenixcontact.com/us/products/1212777>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-RC 2,5 CUS - Crimping pliers



1212777

<https://www.phoenixcontact.com/us/products/1212777>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
-----------------------------------------	-------------------------------------------------------------------------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)