

# WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows WIREFOX 4 CUS

Stripping tool, laser marked according to customer specifications, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

## Product description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

## Your advantages

- Flexible, adjustable limit stop for the stripping length
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

## Commercial data

Item number	1212760
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH312V
GTIN	4046356942768
Weight per piece (including packing)	214 g
Weight per piece (excluding packing)	207.9 g
Country of origin	SE

# WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Stripping tool

Application

Abisolieren von Leitungen und Leiter

### Connection data

#### Conductor connection

Cross section range, metric

0.02 mm<sup>2</sup> ... 10 mm<sup>2</sup> (Stripping range)

1.5 mm<sup>2</sup> (Cutting zone)

Cross section range AWG

34 ... 8 (Stripping range)

16 (Cutting zone)

Stripping length

2 mm ... 18 mm

### Dimensions

Width

20 mm

Height

90 mm

Length

191 mm

### Material specifications

Color

black/green

# WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212760>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

## Classifications

### ECLASS

ECLASS-13.0	21043706
ECLASS-15.0	21043706

### ETIM

ETIM 10.0	EC002109
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# WIREFOX 10 CUS - Stripping tool



1212760

<https://www.phoenixcontact.com/us/products/1212760>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)