MICROFOX-S ESD_DB - Diagonal cutter

1212804

https://www.phoenixcontact.com/us/products/1212804

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ESD electronic diagonal cutter, round head, without chamfer, with opening spring, non-reflective coating and phosphate-treated, 2-component handle, cutting capacity diameter: soft 0.2 ... 2. 0 mm; medium hard 1 mm, type of packaging: with holder for sales display (backcard)

Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept a different ESD-compliant material. In future, the tools will be supplied with plastic handles in black/turquoise. This does not affect the function or quality of the ESD pliers.

Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically designed two-component handles for fatigue-proof and non-slip use
- The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- Made from special high-grade tool steel
- Screwed precision joint for permanent stability and optimum results

Commercial data

Item number	1212804
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BH31
Product key	BH3152
GTIN	4046356994675
Weight per piece (including packing)	105.7 g
Weight per piece (excluding packing)	84.9 g
Customs tariff number	82032000
Country of origin	DE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Electronics pliers

Electrical properties

Fuse	DIN EN 61340-5-1/VDE 0300-5-1, DIN EN 61340-2-3/VDE 0300-2-3

Dimensions

Length	110 mm

Material specifications

Color	multicolored (RAL -)
Material	Steel
Coating	phosphatized

Classifications

ECLASS

ECLASS-13.0	21043711
ECLASS-15.0	21043711

ETIM

ETIM 10.0	EC000165

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com