

# MICROFOX-SB\_DB - Diagonal cutter



1212805

<https://www.phoenixcontact.com/us/products/1212805>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component handle, cutting capacity diameter: soft 0.2 ... 2.0 mm; medium hard 1.2 mm; hard 0.5 mm, type of packaging: with holder for sales display (backcard)

## Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically designed two-component handles for fatigue-proof and non-slip use
- Through-connected joint for permanent stability and optimum distribution of force
- Mirror-polished and oiled metal surfaces, which provide maximum rust protection
- Made from special high-grade tool steel
- For a variety of applications

## Commercial data

Item number	1212805
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BH31
Product key	BH3151
GTIN	4046356994699
Weight per piece (including packing)	109.8 g
Weight per piece (excluding packing)	104.11 g
Customs tariff number	82032000
Country of origin	DE

# MICROFOX-SB\_DB - Diagonal cutter



1212805

<https://www.phoenixcontact.com/us/products/1212805>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Electronics pliers

### Dimensions

Length

115 mm

# MICROFOX-SB\_DB - Diagonal cutter



1212805

<https://www.phoenixcontact.com/us/products/1212805>

## Classifications

### ECLASS

ECLASS-13.0	21043711
ECLASS-15.0	21043711

### ETIM

ETIM 10.0	EC000165
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# MICROFOX-SB\_DB - Diagonal cutter



1212805

<https://www.phoenixcontact.com/us/products/1212805>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	3.323 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)