

UNIFOX-PE VDE_DB - Needle-nose pliers



1212818

<https://www.phoenixcontact.com/us/products/1212818>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Needle-nose pliers, angled design, with opening spring and locking device, finely notched gripping surface, 1.5 mm² and 2.5 mm² can be stripped, integrated M8 - M10 ring wrench, VDE 1000 V AC/1500 V DC tested, type of packaging: with holder for sales display (backcard)

Your advantages

- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC
- The tools feature ergonomic two-component safety handles
- Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)

Commercial data

Item number	1212818
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BH31
Product key	BH3162
GTIN	4046356994835
Weight per piece (including packing)	317.9 g
Weight per piece (excluding packing)	317.9 g
Customs tariff number	82032000
Country of origin	DE

UNIFOX-PE VDE_DB - Needle-nose pliers



1212818

<https://www.phoenixcontact.com/us/products/1212818>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Universal tools

Dimensions

Length

200 mm

Material specifications

Color

black

Standards and regulations

Tests

DIN EN 60900 (VDE 0682 PART 201)

DIN ISO 5745

UNIFOX-PE VDE_DB - Needle-nose pliers



1212818

<https://www.phoenixcontact.com/us/products/1212818>

Classifications

ECLASS

ECLASS-13.0	21043816
ECLASS-15.0	21043816

ETIM

ETIM 10.0	EC000835
-----------	----------

UNSPSC

UNSPSC 21.0	27112100
-------------	----------

UNIFOX-PE VDE_DB - Needle-nose pliers



1212818

<https://www.phoenixcontact.com/us/products/1212818>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com