

CUTFOX-SE - Diagonal cutter



1212832

<https://www.phoenixcontact.com/us/products/1212832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Diagonal cutter, angled design, size: 180 mm



Your advantages

- Cutting harder materials with minimal effort due to high leverage
- Special tool steel for permanent use
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Precision cutting edge for soft and hard wire

Commercial data

Item number	1212832
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH311S
GTIN	4055626045511
Weight per piece (including packing)	278.5 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	82032000
Country of origin	DE

CUTFOX-SE - Diagonal cutter



1212832

<https://www.phoenixcontact.com/us/products/1212832>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Cutting tool
Application	Aluminum
	Copper
Product property	25° angled head
	Extended blade
	Inductively hardened precision cutting edge
	Ergonomic two-component handle
	Minimum force required
	Mirror-polished, matt chrome-plated surface
	Special tool steel, die-forged and oil-hardened\
	~ 62 HRC

Dimensions

Length	180 mm
--------	--------

Material specifications

Color	multicolored (RAL -)
-------	----------------------

Cable/line

External cable diameter	≤ 11.00 mm
	0.2 mm ... 11 mm

CUTFOX-SE - Diagonal cutter



1212832

<https://www.phoenixcontact.com/us/products/1212832>

Classifications

ECLASS

ECLASS-13.0	21043711
ECLASS-15.0	21043711

ETIM

ETIM 9.0	EC000165
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CUTFOX-SE - Diagonal cutter



1212832

<https://www.phoenixcontact.com/us/products/1212832>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com