

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser-inscribed to customer specifications, pliers and properties as in CRIMPFOX CENTRUS 6H

Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Ideal for TWIN ferrule
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping

Commercial data

Item number	1213166
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4055626212708
Weight per piece (including packing)	472.8 g
Weight per piece (excluding packing)	472 g
Country of origin	SE

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

HEX crimp

Crimping position 1

Min. cross section

0.14 mm²

Max. cross section

6 mm²

AWG min

26

AWG max

10

Connection data

Conductor connection

Cross section range, metric

0.14 mm² ... 6 mm²

Cross section range AWG

26 ... 10

Dimensions

Width

70 mm

Height

21 mm

Length

180 mm

Material specifications

Color

black/green

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1213166>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com