

ME MAX 45 PLATE YE - Insertion plate



1236752

<https://www.phoenixcontact.com/us/products/1236752>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 41.8 mm, height: 73.6 mm, depth: 1 mm, color: yellow (similar RAL 1018)



Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	1236752
Packing unit	10 pc
Minimum order quantity	500 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4063151348274
Weight per piece (including packing)	3.747 g
Weight per piece (excluding packing)	3.61 g
Country of origin	DE

ME MAX 45 PLATE YE - Insertion plate



1236752

<https://www.phoenixcontact.com/us/products/1236752>

Technical data

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX 45..
Ventilation openings present	no

Dimensions

Width	41.8 mm
Height	73.6 mm
Depth	1 mm

Material specifications

Color (Insertion plate)	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

PCB data

Type of PCB mount	Latching
-------------------	----------

Mounting

Mounting type	Slot
---------------	------

ME MAX 45 PLATE YE - Insertion plate



1236752

<https://www.phoenixcontact.com/us/products/1236752>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1236752>



UL Recognized

Approval ID: E240868

ME MAX 45 PLATE YE - Insertion plate



1236752

<https://www.phoenixcontact.com/us/products/1236752>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX 45 PLATE YE - Insertion plate



1236752

<https://www.phoenixcontact.com/us/products/1236752>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.035 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com