

# CUTFOX-SE LM\_DB - Diagonal cutter



1212839

<https://www.phoenixcontact.com/us/products/1212839>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electrician's diagonal cutter, angled shape, with stripping and crimp area, size: 180 mm, packaging type: with bracket for sales display (backcard)

## Your advantages

- The tools feature ergonomic two-component safety handles
- Optimum leverage for easy and effortless work
- Inductively hardened blades for long-term stable cutting performance
- Can strip (1.5 mm<sup>2</sup> and 2.5 mm<sup>2</sup>), crimp (1.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>), cut brass screws, and bend eyes (diameter: 4, 5, 6 mm)

## Commercial data

Item number	1212839
Packing unit	6 pc
Minimum order quantity	6 pc
Product key	BH311S
GTIN	4055626045597
Weight per piece (including packing)	299.45 g
Weight per piece (excluding packing)	299.45 g
Country of origin	DE

# CUTFOX-SE LM\_DB - Diagonal cutter



1212839

<https://www.phoenixcontact.com/us/products/1212839>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Cutting tool

Application

Al , Cu

### Dimensions

Length

180 mm

### Material specifications

Color

multicolored (RAL -)

### Cable/line

External cable diameter

0.2 mm ... 11 mm

# CUTFOX-SE LM\_DB - Diagonal cutter



1212839

<https://www.phoenixcontact.com/us/products/1212839>

## Classifications

### ECLASS

ECLASS-13.0	21043711
ECLASS-15.0	21043711

### ETIM

ETIM 10.0	EC000165
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CUTFOX-SE LM\_DB - Diagonal cutter



1212839

<https://www.phoenixcontact.com/us/products/1212839>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)