

# CA-000000090DNX - Housing for circular connector



1244392

<https://www.phoenixcontact.com/us/products/1244392>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Housing for circular connector, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, cable diameter range: 3 mm ... 14.5 mm, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Commercial data

Item number	1244392
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABRAEI
GTIN	4063151408572
Weight per piece (including packing)	88.4 g
Weight per piece (excluding packing)	85.891 g
Country of origin	DE

1244392

<https://www.phoenixcontact.com/us/products/1244392>

## Technical data

### Notes

Order information:	Order contact inserts separately
Order information:	When using a specific cable with Ø 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786601)

### Product properties

Product type	Circular connector housing
Series	CA

### Connector

#### Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

# CA-000000090DNX - Housing for circular connector



1244392

<https://www.phoenixcontact.com/us/products/1244392>

## Classifications

### ECLASS

ECLASS-13.0

27440224

### ETIM

ETIM 9.0

EC003556

### UNSPSC

UNSPSC 21.0

39121100

1244392

<https://www.phoenixcontact.com/us/products/1244392>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)