

PROT-M12 FS-M-CHAINX - Sealing cap



1239603

<https://www.phoenixcontact.com/us/products/1239603>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing cap, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)



Your advantages

- Reliable protection of unoccupied slots during transport and use in the field
- Protected against splash water and dust by the internal seal
- Easy assembly by hand or using a wrench

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1239603 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AB28 |
| Product key | ABQZAB |
| GTIN | 4063151425425 |
| Weight per piece (including packing) | 13.23 g |
| Weight per piece (excluding packing) | 12.936 g |
| Customs tariff number | 74198090 |
| Country of origin | DE |

PROT-M12 FS-M-CHAINX - Sealing cap



1239603

<https://www.phoenixcontact.com/us/products/1239603>

Technical data

Product properties

| | |
|--------------|----------------|
| Product type | Protective cap |
| Thread type | M12 |

Material specifications

| | |
|---------------|-----------------|
| Material | CuZn/Ni (Chain) |
| Material Seal | NBR |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C |
|---|------------------|

PROT-M12 FS-M-CHAINX - Sealing cap



1239603

<https://www.phoenixcontact.com/us/products/1239603>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440208 |
| ECLASS-15.0 | 27440208 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002314 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

PROT-M12 FS-M-CHAINX - Sealing cap



1239603

<https://www.phoenixcontact.com/us/products/1239603>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com