

# SAC-12P-MS/30,0-35T SH SCO - Sensor/actuator cable



1247748

<https://www.phoenixcontact.com/us/products/1247748>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, Plug straight, on free cable end

## Commercial data

Item number	1247748
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF19
Product key	AF1CNA
GTIN	4063151350550
Weight per piece (including packing)	2,755 g
Weight per piece (excluding packing)	2,755 g
Customs tariff number	85444290
Country of origin	DE

# SAC-12P-MS/30,0-35T SH SCO - Sensor/actuator cable



1247748

<https://www.phoenixcontact.com/us/products/1247748>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Shielded	yes

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	1.5 A

### Connection data

#### Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

### Connector

#### Connection 1

Type	Plug straight
------	---------------

#### Connection 2

Type	free cable end
------	----------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67
	IP68

# SAC-12P-MS/30,0-35T SH SCO - Sensor/actuator cable



1247748

<https://www.phoenixcontact.com/us/products/1247748>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-12P-MS/30,0-35T SH SCO - Sensor/actuator cable



1247748

<https://www.phoenixcontact.com/us/products/1247748>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)