

BASE/U/RAIL DIVIDER - Partition plate



1267397

<https://www.phoenixcontact.com/us/products/1267397>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP I/O marshalling partition plate for safe isolation between non-Ex i and Ex i assembled base modules, for universal use in UM-PRO ...MSTB... design
The partition plate is mounted directly on the DIN rail at the end of the base module.

Your advantages

- Rail mounted divider at the end of the VIP base module provides separation between circuits
- Durable, sleek design

Commercial data

Item number	1267397
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C480
Product key	DK115Z
GTIN	4063151387105
Weight per piece (including packing)	46.2 g
Weight per piece (excluding packing)	46.2 g
Customs tariff number	39269097
Country of origin	US

BASE/U/RAIL DIVIDER - Partition plate



1267397

<https://www.phoenixcontact.com/us/products/1267397>

Technical data

Product properties

Product type	Partition plate
Product family	VIP I/O-Marshalling

Mounting

Mounting type	any
---------------	-----

Material specifications

Color	black (RAL 9005)
Material	Thermoplastics

Dimensions

Width	1.5 mm
Height	202.3 mm
Depth	110.65 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

BASE/U/RAIL DIVIDER - Partition plate



1267397

<https://www.phoenixcontact.com/us/products/1267397>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121421
-------------	----------

BASE/U/RAIL DIVIDER - Partition plate



1267397

<https://www.phoenixcontact.com/us/products/1267397>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com