

# TM-RIBBON 64 BK 103 - Ink ribbon



1255598

<https://www.phoenixcontact.com/us/products/1255598>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, For the E-WML... product group in combination with the THERMOMARK E.WRAP applicator, length: 300 m, roll length: 300 m, width: 64 mm, color: black

## Product description

The TM-RIBBON 64 BK 103 is a thermal transfer ink ribbon, which is suitable for automated processing with the THERMOMARK E.WRAP applicator in combination with the THERMOMARK E.300 D/600 D printers and the markers from the E-WML... product family.

## Your advantages

- The ink ribbon is designed for E-WML... wire-wrap labels
- When combined with the right labels, the printing is highly resistant to solvents and mechanical influences

## Commercial data

Item number	1255598
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4063151362539
Weight per piece (including packing)	209 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	96121010
Country of origin	CN

# TM-RIBBON 64 BK 103 - Ink ribbon



1255598

<https://www.phoenixcontact.com/us/products/1255598>

## Technical data

### Product properties

Product type	Ink ribbon
--------------	------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Dimensions

Width	64 mm
Length	300000 mm
Length of roll	300 m

### Material specifications

Color	black (RAL 9005)
Material	Resin

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

# TM-RIBBON 64 BK 103 - Ink ribbon



1255598

<https://www.phoenixcontact.com/us/products/1255598>

## Classifications

### ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

### ETIM

ETIM 10.0	EC001694
-----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# TM-RIBBON 64 BK 103 - Ink ribbon



1255598

<https://www.phoenixcontact.com/us/products/1255598>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)