

SAC-5P-M12MRB/10,0-PUR - Sensor/actuator cable



1299565

<https://www.phoenixcontact.com/us/products/1299565>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable

Commercial data

Item number	1299565
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4063151543402
Weight per piece (including packing)	311.9 g
Weight per piece (excluding packing)	311.9 g
Country of origin	PL

SAC-5P-M12MRB/10,0-PUR - Sensor/actuator cable



1299565

<https://www.phoenixcontact.com/us/products/1299565>

Technical data

Product properties

Product type	Sensor/actuator cable
--------------	-----------------------

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Connection data

Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1299565>

UL Listed Approval ID: FILE E 221474				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	4 A	-	-

SAC-5P-M12MRB/10,0-PUR - Sensor/actuator cable



1299565

<https://www.phoenixcontact.com/us/products/1299565>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MRB/10,0-PUR - Sensor/actuator cable



1299565

<https://www.phoenixcontact.com/us/products/1299565>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com