

# SACC-FP-F-M12/M14-9 THR WS - Housing screw connection



1286346

<https://www.phoenixcontact.com/us/products/1286346>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Socket, M12-Screw locking mechanism, THR solder connection, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1286346
Packing unit	100 pc
Minimum order quantity	500 pc
Product key	ABQACI
GTIN	4063151511609
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	9.2 g
Country of origin	DE

# SACC-FP-F-M12/M14-9 THR WS - Housing screw connection



1286346

<https://www.phoenixcontact.com/us/products/1286346>

## Technical data

### Product properties

Product type	Circular connector housing
Thread type	M12

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Connector

#### Connection 1

Head design	Socket
Head thread type	M12
Head locking type	Screw locking mechanism

### Environmental and real-life conditions

#### Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------

### Mounting

Mounting type	Front mounting
---------------	----------------

# SACC-FP-F-M12/M14-9 THR WS - Housing screw connection



1286346

<https://www.phoenixcontact.com/us/products/1286346>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-FP-F-M12/M14-9 THR WS - Housing screw connection



1286346

<https://www.phoenixcontact.com/us/products/1286346>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	de505b01-1703-4696-b723-c3eeb808a5e3

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)