

TM-RIBBON 30 BK 103 - Ink ribbon



1309076

<https://www.phoenixcontact.com/us/products/1309076>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for the E-WM... product group in combination with the THERMOMARK E.WIRE applicator, length: 300 m, roll length: 300 m, width: 30 mm, color: black

Product description

The TM-RIBBON 30 BK 103 is a thermal transfer ink ribbon, which is suitable for automated processing with the THERMOMARK E.WIRE applicator. When combined with the THERMOMARK E.300 (D) / 600 (D) printers, the desired marking can be printed on the special markers from the E-WM... product family

Your advantages

- The TM-RIBBON 30 BK 103 thermal transfer ink ribbon is suitable for automated processing with the THERMOMARK E.WIRE applicator
- For efficient use of the entire ink ribbon, the width is optimally tailored to the E-WM... product group
- When combined with materials from the E-WM product group, the printing is highly resistant to solvents and mechanical influences

Commercial data

Item number	1309076
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4063151560409
Weight per piece (including packing)	102.9 g
Weight per piece (excluding packing)	102.9 g
Customs tariff number	96121010
Country of origin	CN

TM-RIBBON 30 BK 103 - Ink ribbon



1309076

<https://www.phoenixcontact.com/us/products/1309076>

Technical data

Product properties

Product type	Ink ribbon
Scope of supply	Ink ribbon

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	30 mm
Length	300 m
Length of roll	300 m

Material specifications

Color	black (RAL 9005)
Material	Resin

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

TM-RIBBON 30 BK 103 - Ink ribbon



1309076

<https://www.phoenixcontact.com/us/products/1309076>

Classifications

ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

ETIM

ETIM 10.0	EC001694
-----------	----------

UNSPSC

UNSPSC 21.0	44103100
-------------	----------

TM-RIBBON 30 BK 103 - Ink ribbon



1309076

<https://www.phoenixcontact.com/us/products/1309076>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com