

# CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/us/products/1314533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for solid contacts from the CK4.0 ED... series, two marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

## Your advantages

- Marked die stations for precise processing of corresponding cross sections
- Rotating positioning aid ensures precise contact positioning in the crimping area

## Commercial data

Item number	1314533
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3135
GTIN	4063151571146
Weight per piece (including packing)	738.6 g
Weight per piece (excluding packing)	738.6 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/us/products/1314533>

## Technical data

### Notes

Note on application	For 6.0 mm <sup>2</sup> ... 10.0 mm <sup>2</sup> turned crimp contacts from the CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts
---------------------	---

### Product properties

Product type	Crimping tool
Compression	Square crimp
Product property	Marked die stations
	Including positioning guide

#### Crimping position 1

Max. cross section	6 mm <sup>2</sup>
AWG max	10

#### Crimping position 2

Max. cross section	10 mm <sup>2</sup>
AWG max	8

### Connection data

#### Conductor connection

Cross section range, metric	6 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section range AWG	10 ... 8

### Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

### Material specifications

Color	black (RAL 9005)
Material	Steel

# CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/us/products/1314533>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1314533>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/us/products/1314533>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-TC HC 10 - Crimping pliers



1314533

<https://www.phoenixcontact.com/us/products/1314533>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)