

SACC-CI-M12FSL-4FE-L180THR_WPD - Contact carrier



1339747

<https://www.phoenixcontact.com/us/products/1339747>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position, Socket, straight, M12, L-coding, THR solder connection

Commercial data

Item number	1339747
Packing unit	60 pc
Minimum order quantity	1,020 pc
Product key	ABQAGW
GTIN	4063151644871
Weight per piece (including packing)	4.588 g
Weight per piece (excluding packing)	3.138 g
Country of origin	DE

SACC-CI-M12FSL-4FE-L180THR_WPD - Contact carrier



1339747

<https://www.phoenixcontact.com/us/products/1339747>

Technical data

Product properties

Product type	Contact insert
Application	Power
Number of positions	5
Connection profile	4+FE
No. of power contacts	5
Seal present	yes
Coding	L
Thread type	M12

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	L

Environmental and real-life conditions

Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------


SACC-CI-M12FSL-4FE-L180THR_WPD - Contact carrier

1339747

<https://www.phoenixcontact.com/us/products/1339747>

Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

SACC-CI-M12FSL-4FE-L180THR_WPD - Contact carrier




1339747

<https://www.phoenixcontact.com/us/products/1339747>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1339747>

 cULus Recognized Approval ID: E468743-20180113				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	63 V	16 A	-	-

SACC-CI-M12FSL-4FE-L180THR_WPD - Contact carrier



1339747

<https://www.phoenixcontact.com/us/products/1339747>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FSL-4FE-L180THR_WPD - Contact carrier



1339747

<https://www.phoenixcontact.com/us/products/1339747>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com