

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/us/products/1324135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement die for CRIMPFOX-TC HC 10, CK 4,0-ED... turned contacts, 2 marked die stations



Your advantages

- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1324135
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Y
GTIN	4063151610487
Weight per piece (including packing)	50.88 g
Weight per piece (excluding packing)	50.88 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/us/products/1324135>

Technical data

Notes

Note on application	For 6.0 mm ² ... 10.0 mm ² turned crimp contacts from the CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts
---------------------	---

Product properties

Product type	Die
Compression	Square crimp

Crimping position 1

Max. cross section	6 mm ²
AWG max	10

Crimping position 2

Max. cross section	10 mm ²
AWG max	8

Connection data

Conductor connection

Cross section range, metric	6 mm ² ... 10 mm ²
Cross section range AWG	10 ... 8

Material specifications

Color	black (RAL 9005)
Material	Steel

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/us/products/1324135>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1324135>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/us/products/1324135>

Classifications

ECLASS

ECLASS-13.0	21043852
ECLASS-15.0	21043852

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/us/products/1324135>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com