


KP BC K6 C2 P7 - Membrane keypad



1337344

<https://www.phoenixcontact.com/us/products/1337344>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Membrane keypad for BC 107,6 and BC 161,6, self-adhesive, conductive silver technology, 6 keys, 2 colors, 7-pos. terminal lug, pitch: 1.0 mm, customizable in the online configurator

Your advantages

- Suitable for different device requirements, thanks to housing versions with and without membrane keypad
- Coordinated housing, keypad, and display design
- Maximum flexibility with many combination options for the housing cover and upper parts
- Customization of membrane keypad via configurator

Commercial data

Item number	1337344
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC05
Product key	ACHBAJ
GTIN	4063151639815
Weight per piece (including packing)	4.01 g
Weight per piece (excluding packing)	4.01 g
Customs tariff number	85371098
Country of origin	DE

KP BC K6 C2 P7 - Membrane keypad



1337344

<https://www.phoenixcontact.com/us/products/1337344>

Technical data

Product properties

Product type	Membrane keypad
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing series	BC
Number of positions	7
Pitch	1 mm
Number of keys	6 (2 x 3)

Dimensions

Length	80 mm (Membrane cable)
Pitch	1 mm
Dimensions	28 mm x 42 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
---------------------------------	------------------

KP BC K6 C2 P7 - Membrane keypad



1337344

<https://www.phoenixcontact.com/us/products/1337344>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

KP BC K6 C2 P7 - Membrane keypad



1337344

<https://www.phoenixcontact.com/us/products/1337344>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com