CRIMPFOX DUO 16S SET - Tool set

1367687

https://www.phoenixcontact.com/us/products/1367687

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, WIREFOX 16/SB, CRIMPFOX DUO 16S, AI SORTI BOX RD, AI SORTI BOX ANT, TOOL-KIT STANDARD EMPTY

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

Commercial data

Item number	1367687
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4063151722128
Weight per piece (including packing)	1,102 g
Weight per piece (excluding packing)	1,100 g
Customs tariff number	82060000
Country of origin	DE

Set consists of

CRIMPFOX DUO 16S - Crimping pliers

1202877

https://www.phoenixcontact.com/us/products/1202877



Crimping pliers, contact type: insulated and uninsulated ferrules, standards/regulations: DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F, cross-section, minimum: 0.14 mm^2, cross-section, maximum: 16 mm^2, for TWIN ferrules up to 2 mm^2 x 6 mm^2, automatic cross-section adjustment, rotating dies, lateral and front entry, crimping: square

WIREFOX 10 - Stripping tool

1212150

https://www.phoenixcontact.com/us/products/1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm^2, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm^2 stranded/1.5 mm^2 solid, replaceable stripping blade

WIREFOX 16/SB - Spare knife

1212153

https://www.phoenixcontact.com/us/products/1212153



Replacement blade for WIREFOX 16, for cables and conductors of 4 - 16 mm^2

AI SORTI BOX RD - Assortment box

3202960

https://www.phoenixcontact.com/us/products/3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

AI SORTI BOX ANT - Assortment box

3202973

https://www.phoenixcontact.com/us/products/3202973



Assortment box, supplied with ferrules in accordance with DIN 46228-4, 50 pcs. AI 4-10 GY, 20 pcs. each AI 6-12 YE, AI 10-12 RD, 10 pcs. AI 16-12 BU

TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

https://www.phoenixcontact.com/us/products/1212423



Tool box, unequipped

Technical data

Notes

General	DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Square crimp

Crimping position 1

Min. cross section	16 mm²
Max. cross section	0.14 mm²
AWG min	26
AWG max	6

Electrical properties

Fuse	DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black (RAL 9005)

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149

UNSPSC

UNSPSC 21.0	27113200

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com