

RAILFIX 35/15 - Mounting adapter



1383151

<https://www.phoenixcontact.com/us/products/1383151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting adapter, for attaching NS 35/15 DIN rails to mounting panels or housing walls of control cabinets, material: Die-cast zinc, mounting type: Screw mounting, color: gray



Commercial data

Item number	1383151
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BE07
Product key	BE72VZ
GTIN	4063151756635
Weight per piece (including packing)	75 g
Weight per piece (excluding packing)	75 g
Customs tariff number	79070000
Country of origin	IT

RAILFIX 35/15 - Mounting adapter

1383151

<https://www.phoenixcontact.com/us/products/1383151>



Technical data

Product properties

Product type	Assembly adapter
Area of application	Machine building
	Plant engineering
	Control cabinet building
	Machine building

Electrical properties

Contact resistance	< 5 mΩ
--------------------	--------

Connection data

Screw thread	M5
Tightening torque	2 Nm

Dimensions

Width	89 mm
Hole width	15 mm
Height	40 mm
Hole height	6.2 mm
Depth	17.8 mm
Hole diameter	4.6 mm (Centering pin)

Material specifications

Color	gray (RAL 7042)
Material	Die-cast zinc

Mounting

Mounting type	Screw mounting
---------------	----------------

RAILFIX 35/15 - Mounting adapter



1383151

<https://www.phoenixcontact.com/us/products/1383151>

Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 10.0	EC001024
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RAILFIX 35/15 - Mounting adapter



1383151
<https://www.phoenixcontact.com/us/products/1383151>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com