

SAC-4P-M12MS/0,2PUR/M12FS35SMC - Sensor/actuator cable



1386986
<https://www.phoenixcontact.com/us/products/1386986>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, Plug straight SPEEDCON, on Socket straight SPEEDCON, cable length: 0.2 m

Commercial data

Item number	1386986
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	AF1CKA
GTIN	4063151764425
Weight per piece (including packing)	19.05 g
Weight per piece (excluding packing)	19.05 g
Country of origin	PL

SAC-4P-M12MS/0,2PUR/M12FS35SMC - Sensor/actuator cable



1386986

<https://www.phoenixcontact.com/us/products/1386986>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
Shielded	no

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

Connector

Connection 1

Type	Plug straight SPEEDCON
Number of positions	4
Locking type	SPEEDCON

Connection 2

Type	Socket straight SPEEDCON
Number of positions	4
Locking type	SPEEDCON

Cable/line

Cable length	0.2 m
--------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67

SAC-4P-M12MS/0,2PUR/M12FS35SMC - Sensor/actuator cable



1386986

<https://www.phoenixcontact.com/us/products/1386986>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1386986>

	UL Listed Approval ID: FILE E 221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	keine			
	60 V	4 A	-	-

	cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	keine			
	60 V	4 A	-	-

	EAC-RoHS Approval ID: RU D-DE.HB35.B.00387			

SAC-4P-M12MS/0,2PUR/M12FS35SMC - Sensor/actuator cable



1386986

<https://www.phoenixcontact.com/us/products/1386986>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M12MS/0,2PUR/M12FS35SMC - Sensor/actuator cable



1386986

<https://www.phoenixcontact.com/us/products/1386986>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.224 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com