

SAC-5P-10,0-500/AD-2L KA - Sensor/actuator cable



1400762

<https://www.phoenixcontact.com/us/products/1400762>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, free cable end, on Valve connector AD (pressure switch), with 2 LEDs, cable length: 10 m

Commercial data

Item number	1400762
Packing unit	25 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1DBA
GTIN	4046356511179
Weight per piece (including packing)	525 g
Weight per piece (excluding packing)	525 g
Country of origin	PL

1400762

<https://www.phoenixcontact.com/us/products/1400762>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	5
No. of cable outlets	1

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Valve connector AD (pressure switch)
------	--------------------------------------

Cable/line

Cable length	10 m
--------------	------

Standards and regulations

Valve connector

Standard designation	Valve connector
Standards/specifications	EN 175301-803

SAC-5P-10,0-500/AD-2L KA - Sensor/actuator cable




1400762

<https://www.phoenixcontact.com/us/products/1400762>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1400762>

 CSAus Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	4 A	-	-

SAC-5P-10,0-500/AD-2L KA - Sensor/actuator cable



1400762

<https://www.phoenixcontact.com/us/products/1400762>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-5P-10,0-500/AD-2L KA - Sensor/actuator cable



1400762

<https://www.phoenixcontact.com/us/products/1400762>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com