

SAC-3P-3,0-PVC/A-1L-Z - Sensor/actuator cable



1400613

<https://www.phoenixcontact.com/us/products/1400613>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sensor/actuator cable, free cable end, on Valve connector A, with 1 LED, Wiring: Z diode



Commercial data

Item number	1400613
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1DAA
GTIN	4046356509541
Weight per piece (including packing)	140 g
Weight per piece (excluding packing)	129.4 g
Country of origin	PL

SAC-3P-3,0-PVC/A-1L-Z - Sensor/actuator cable



1400613

<https://www.phoenixcontact.com/us/products/1400613>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
--------------	--

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Valve connector A
Protective circuit	Z diode

SAC-3P-3,0-PVC/A-1L-Z - Sensor/actuator cable





1400613

<https://www.phoenixcontact.com/us/products/1400613>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1400613>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	4 A	-	-

 CSAus Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	4 A	-	-

SAC-3P-3,0-PVC/A-1L-Z - Sensor/actuator cable



1400613

<https://www.phoenixcontact.com/us/products/1400613>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-3P-3,0-PVC/A-1L-Z - Sensor/actuator cable



1400613

<https://www.phoenixcontact.com/us/products/1400613>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com