# BNB-ZB 5,2,LGS:FORTL.ZAHLEN 41-50 - Marker for terminal blocks

1401802:0041

https://www.phoenixcontact.com/us/products/1401802:0041

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



BNB Zack marker strip, 10-section, divisible, horizontally labeled with the consecutive numbers: 41 ... 50, white, mounting type: plug in

## Commercial data

| | |
|---|---|
| Item number | 1401802:0041 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG05 |
| Product key | BG2122 |
| GTIN | 4017918554163 |
| Weight per piece (including packing) | 0.46 g |
| Weight per piece (excluding packing) | 0.34 g |
| Customs tariff number | 49119900 |
| Country of origin | PL |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Terminal marker |

Marking

| | |
|---|---|
| Printing | 41 ... 50 |

### Mounting

| | |
|---|---|
| Mounting type | plug in |

### Material specifications

| | |
|---|---|
| Color | white (RAL 9010) |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

### Dimensions

| | |
|---|---|
| Width | 4 mm |
| Height | 4 mm |

Text field

| | |
|---|---|
| Text field width | 4.00 mm |
| Text field height | 4.00 mm |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000761 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39131500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com