

# SAC-3P-20,0-534/AD 180 BM - Sensor/actuator cable



1403217

<https://www.phoenixcontact.com/us/products/1403217>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable

## Commercial data

Item number	1403217
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF07
Product key	AF1DBA
GTIN	4046356643443
Weight per piece (including packing)	937.1 g
Weight per piece (excluding packing)	924.6 g
Customs tariff number	85444290
Country of origin	PL

1403217

<https://www.phoenixcontact.com/us/products/1403217>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
--------------	--

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Connection data

#### Conductor connection

Tightening torque	0.6 Nm
-------------------	--------

### Electrical properties

Nominal voltage $U_N$	230 V AC
	230 V DC
Nominal current $I_N$	4 A

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67

### Standards and regulations

#### Valve connector

Standard designation	Valve connector
Standards/specifications	EN 175301-803

# SAC-3P-20,0-534/AD 180 BM - Sensor/actuator cable




1403217

<https://www.phoenixcontact.com/us/products/1403217>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1403217>

 <b>CSAus</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	6 A	-	-

1403217

<https://www.phoenixcontact.com/us/products/1403217>

## Classifications

### ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

1403217

<https://www.phoenixcontact.com/us/products/1403217>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
-------------------------------------	---

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)