

# VS-TO-RO-MCBK-F1421/1421 - Terminal outlet



1404294

<https://www.phoenixcontact.com/us/products/1404294>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal outlet, degree of protection: IP65/IP67, CAT5 (IEC 11801:2002), material: Metal, color: black

Terminal outlet 2xM12 4-pos.

## Your advantages

- Easy installation, thanks to captive cover screws
- Robust design
- Integrated cable management system

## Commercial data

Item number	1404294
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOEB
GTIN	4046356305396
Weight per piece (including packing)	719.2 g
Weight per piece (excluding packing)	719.2 g
Customs tariff number	85369095
Country of origin	DE

# VS-TO-RO-MCBK-F1421/1421 - Terminal outlet



1404294

<https://www.phoenixcontact.com/us/products/1404294>

## Technical data

### Product properties

Product type	Data plug
Type	M12
Connection profile	M12
Number of slots	2

### Electrical properties

Transmission medium	Copper
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

### Material specifications

Color	black
Housing material	Metal

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C

### Mounting

Mounting type	Screw mounting
---------------	----------------

# VS-TO-RO-MCBK-F1421/1421 - Terminal outlet



1404294

<https://www.phoenixcontact.com/us/products/1404294>

## Classifications

### ECLASS

ECLASS-13.0

27440318

### ETIM

ETIM 9.0

EC002597

### UNSPSC

UNSPSC 21.0

43223300

1404294

<https://www.phoenixcontact.com/us/products/1404294>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f9eba18c-a4b2-4a81-a9a4-434ecb58bb9b

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)