

SAC-3P-0,27-121/A-1L 0,08 AE - Sensor/actuator cable



1404905

<https://www.phoenixcontact.com/us/products/1404905>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-pos., PVC, RAL 7021 (black-gray), free cable end with wires measuring 8 cm in length and ferrules, to valve connector A, with 1 LED

Commercial data

Item number	1404905
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1DAA
GTIN	4046356727433
Weight per piece (including packing)	49.06 g
Weight per piece (excluding packing)	49.06 g
Country of origin	PL

SAC-3P-0,27-121/A-1L 0,08 AE - Sensor/actuator cable



1404905

<https://www.phoenixcontact.com/us/products/1404905>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
No. of cable outlets	1

Material specifications

Seal material	TPU
Material housing valve plug	TPU
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn
Outer sheath, material	PVC

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	24 V DC

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Valve connector A
Material	CuSn (Contact)
	Sn (Contact surface)
	PA 6.6 (Contact carrier)
	TPU (Housing)

Cable/line

Cable length	0.27 m
Outer sheath, material	PVC
External sheath, color	black RAL 9005

SAC-3P-0,27-121/A-1L 0,08 AE - Sensor/actuator cable



1404905

<https://www.phoenixcontact.com/us/products/1404905>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

SAC-3P-0,27-121/A-1L 0,08 AE - Sensor/actuator cable



1404905

<https://www.phoenixcontact.com/us/products/1404905>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com