

# Q 1,5 N-GY-9,3 - Nut

1405124

<https://www.phoenixcontact.com/us/products/1405124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Nut, connection method: IDC connection, 0.75 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, gray

## Your advantages

- Robust throughout: housing with IP65/IP67 protection for a wide range of applications

## Commercial data

Item number	1405124
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	AF6UCX
GTIN	4046356749312
Weight per piece (including packing)	8.866 g
Weight per piece (excluding packing)	8.008 g
Country of origin	PL

# Q 1,5 N-GY-9,3 - Nut

1405124

<https://www.phoenixcontact.com/us/products/1405124>



## Technical data

### Product properties

Product type	Installation pressure nut
--------------	---------------------------

### Connection data

#### Connection technology

Connection method On the field side	IDC connection
Frequency of connections between conductors of the same cross section	10

#### Conductor connection

Conductor cross-section flexibel	0.75 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section solid	0.75 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Connection cross section AWG	18 ... 16

# Q 1,5 N-GY-9,3 - Nut

1405124

<https://www.phoenixcontact.com/us/products/1405124>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405124>



**EAC**

Approval ID: RU C-DE.A\*30.B.01102

# Q 1,5 N-GY-9,3 - Nut



1405124

<https://www.phoenixcontact.com/us/products/1405124>

## Classifications

### ECLASS

ECLASS-13.0	27440691
ECLASS-15.0	27440691

### ETIM

ETIM 10.0	EC002863
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# Q 1,5 N-GY-9,3 - Nut



1405124

<https://www.phoenixcontact.com/us/products/1405124>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)